



VersaMount Mounting System by Trek-Tech™



VersaMount in use on TrekPod for macro photography



VersaMount in use on TrekPod to enable seated observation

VersaMount™ makes your TrekPod™ an even more versatile tool. VersaMount enables:

- Picture taking from a seated or kneeling position
- Macro photography on TrekPod & many tripods
- Seated long-range observation with powerful spotting scopes

VersaMount can quickly be secured anywhere along a TrekPod's upper or lower tubes and be used to mount a MagMount™ or ShotRest™ mount for use with Mag Adapter-mounted devices.

Like TrekPod and TrekPod II™, VersaMount has an industry standard 1/4"-20 threaded stud, so almost any photographic or optical accessory can be attached.

VersaMount works on virtually any tube with a diameter between 14.25mm and 29.5mm, which equates to 0.56 inches (9/16") and 1.16 inches (just over 1-1/8"). Manufactured from high-strength aluminum alloy, VersaMount is extremely strong, yet weighs less than 3 ounces and fits in your pocket when not in use.

SPECIFICATIONS:

Limited Lifetime Warranty. For complete warranty details visit trek-tech.com, call us at 503.450.0030, or ask your retailer for details.

VersaMount Weight	2.9 oz/82.2gr
Mounting Stud	Industry Standard 1/4"-20
Tube Diameter Range	.56" to 1.16" (14.25mm to 29.5mm)
Approximate Width	1.72" (43.6 mm)
Thickness, arm	.63" (16 mm)
Thickness, mounting base, including stud	1" (26 mm)
Length, minimum	5.8" (147.6 mm)
Length, maximum	6.4" (161.4 mm)
Material (primary)	Aluminum Alloy



Copyright © 2006 Taylor Sen



VersaMount in use on tripod leg for auxiliary camera mount



VersaMount with and without MagMount Attached

Trek Technologies LLC
 15858 SW Upper Boones Ferry Road
 Lake Oswego, OR 97035 USA
 503.459.0030 • www.trek-tech.com

